



Sample gas cooler TC-Standard+ X2

In emission measurement, process control relies on prompt and exact determination of the operating parameters.

Here, gas analysis is the key for safe and efficient control of process flows, environmental protection and quality assurance. This benefits controlling flue gas emission in power stations as well as measurements in small combustion plants or exhaust gas analysis in automotive engineering.

Many of the analysis processes used in these fields require extracting the sample gas. This inevitably also extracts process-related contamination such as particles or moisture. These in turn can impact the measurement results or damage the measuring cells. The sample gas must therefore be conditioned before entering the analyser.

Many applications require equipment which can be used in explosive areas. This is where the TC-Standard+ X2 series provides solutions for Zone 2 or Class I, Division 2.

ATEX and IECEx Zone 2 approval

FM C-US approval for Class I, Division 2

Compact design: Pre-installed and ready to connect

Low maintenance costs based on easy accessibility

One gas path

Optimised heat exchanger type 2 in Duran glass or PVDF

Adjustable outlet dew point and alarm thresholds

Low operating noise

Rated capacity 100/90 kJ/h, 40 °C/50 °C version

Dew point stability 0.1 °C

Status display and output

Cooling block temperature display

Moisture detector connection, analog output, filter, and peristaltic pump optional



Overview

The TC-Standard+ X2 series was designed specifically for the requirements in so-called automated measuring systems (AMS) according to EN 15267-3. The series connection of the heat exchangers will cool in two cycles to minimise wash out effects.

The Peltier coolers are distinguished according to cooling capacity/operating temperature. This classification is reflected in the type designation. The exact item number of the model defined by you is determined by the model code in the category ordering information.

Application	Standard applications	
Operating temperature	40 °C	50 °C
2 heat exchangers in series	TC-Standard+ 6121 X2	TC-Standard+ 6122 X2

Additional components which every conditioning system should feature can optionally be integrated:

- Peristaltic pump for condensate separation,
- Filter,
- Moisture detector.

This allows for various configurations of cooler and options. Here the approach is to simplify creating a complete system in a cost-efficient way through pre-installed components with hoses connected. We further paid attention to easy access to wear parts and consumables.

Description of functions

The cooler is controlled by a microprocessor. With the factory preset the control already incorporates the various characteristics of the built-in heat exchangers.

The programmable display shows the block temperature in the selected display unit (°C / °F) (factory preset °C). Application-specific settings can easily be configured guided by the menu, using the 5 buttons. For one, this applies to the target outlet dew point, which can be set from 2 to 20 °C (36 °F to 68 °F) (factory preset 5 °C/41 °F).

And then the warning thresholds can be adjusted for low and excess temperature. These are set relative to the outlet dew point τ_a setting.

For the low temperature the range is $\tau_a -1$ to -3 K (at a minimum 1 °C/ 34 °F cooling block temperature), for the excess temperature the range is $\tau_a +1$ to $+7$ K. The factory presets for both values are 3 K.

The flashing display and the status relays indicate the conditions are below or above the configured warning range (e.g. after switching on).

The status output can e.g. be used to control the sample gas pump to allow for the gas flow to only be switched on once the permissible cooling range has been reached or shut off the pump in the event of a moisture detector alarm.

The separated condensate can be drained via connected peristaltic pumps or add-on automatic condensate drains.

Fine mesh filters can also be used, which in turn can be installed in optional moisture detectors.

The glass dome allows the dirt level of the filter element to easily be determined.

The moisture detector is easy to remove. This may be required if a condensate enters the cooler due to a malfunction and the peristaltic pump or the automatic condensate drain is unable to remove it.

Gas cooler technical data

Gas Cooler Technical Data						
Ready for operation	after max. 10 minutes					
Ambient temperature	5 °C to 50 °C					
Gas output dew temperature preset: adjustable:	5 °C 2 °C...20 °C					
IP rating	IP 20					
Mechanical load	Tested based on DNV-GL CG0339 vibration class A (0.7g) 2 Hz-13.2 Hz amplitude ± 1.0 mm 13.2 Hz -100 Hz acceleration					
Housing	Stainless steel, brushed					
Packaging dimensions	approx. 355 x 220 x 205 mm					
Weight incl. heat exchanger	approx. 7.5 kg approx. 6 kg (for 24 V DC) approx. 9 kg at full expansion stage					
Electrical data	Unit without add-on			Unit with add-on (1 peristaltic pump)		
	24 V DC	230 V AC	115 V AC	24 V DC	230 V AC	115 V AC
	±10%	+5/-10%	+5/-10%	±10%	+5/-10%	+5/-10%
	-	50/60 Hz	50/60 Hz	-	50/60 Hz	50/60 Hz
	5 A	0.6 A	1.2 A	5.5 A	0.7 A	1.4 A
	120 W	110 W / 140 VA		130 W	130 W / 160 VA	
Recommended fuse (characteristic: delayed action)	6.3 A	1.25 A	2.5 A	6.3 A	1.25 A	2.5 A
Status output switching capacity	max. 250 V AC, 150 V DC 2 A, 50 VA, potential-free					
Electrical Connections	Plug per EN 175301-803					
Gas connections and condensate outlet	Heat exchanger see table "Heat Exchanger Overview" Filter, moisture detector adapter G1/4 or NPT 1/4"					
Parts in contact with media Filter: Moisture detector: Heat exchanger: Peristaltic pump: Tubing:	see "Technical Data - Options" see "Technical Data - Options" see table "Heat Exchanger Overview" see "Technical Data - Options" PTFE/Viton					
Markings:	FM18ATEX0012X: II 3 G Ex ec nC IIC T4 Gc IECEx FMG 18.0005X: Ex ec nC IIC T4 Gc FM18US0021X/FM18CA0010X: CL I DIV 2 GP ABCD RU C-DE.HA65.B.00608/20					

Technical Data - Options
Analogue Output Cooler Temperature Technical Data

Signal	4-20 mA or 2-10 V corresponds to -20 °C to +60 °C cooler temperature
Connection	M12x1 plug, DIN EN 61076-2-101

Technical Data FF-3-N Moisture Detector

Ambient temperature	3 °C to 50 °C
max. operating pressure with FF-3-N	2 bar
Material	PVDF, PTFE, epoxy resin, stainless steel 1.4571, 1.4576

Technical Data peristaltic pump CPdouble X2


Ambient temperature	0 °C to 50 °C
Flow rate	0.3 L/h (50 Hz) / 0.36 L/h (60 Hz) with standard hose
Vacuum inlet	max. 0.8 bar
Pressure inlet	max. 1 bar
Outlet pressure	1 bar
Hose	4 x 1.6 mm
Degree of protection	IP 44
Materials	
Hose:	Norprene (standard), Marprene, Fluran
Connections:	PVDF

AGF-PV-30-F2 Filter Technical Data


Ambient temperature	3 °C to 100 °C
max. operating pressure with filter	4 bar
Filter surface	60 cm ²
Filter fineness	2 µm
Dead volume	57 ml
Materials	
Filter:	PVDF, Duran glass (parts in contact with media)
Seal:	Viton
Filter element:	sintered PTFE

Performance curves
Model TC-Standard+ 6121 (X2)

Rated cooling capacity (at 25 °C)	100 kJ/h
Max. Ambient temperature	40 °C
Dew point fluctuations static	± 0.1 K
in the entire specification range	± 1.5 K
Temperature difference between heat exchangers	< 0.5 K


Model TC-Standard+ 6122 (X2)

Rated cooling capacity (at 25 °C)	90 kJ/h
Max. Ambient temperature	50 °C
Dew point fluctuations static	± 0.1 K
in the entire specification range	± 1.5 K
Temperature difference between heat exchangers	< 0.5 K



Note: The limit curves for the heat exchangers MTV-2 and MTG-2 apply to a dew point of 50 °C.

Heat exchanger description

The energy content of the sample gas and the required cooling capacity of the gas cooler is determined by three parameters: gas temperature ϑ_G , dew point τ_e (moisture content) and volume flow v . The outlet dew point rises with increasing energy content of the gas. The following limits for the maximum flow are specified for a standard operating point of $\tau_e = 40^\circ\text{C}$ and $\vartheta_G = 70^\circ\text{C}$. The maximum flow v_{\max} in NI/h of cooled air indicated, so after moisture has condensed. Values may differ for other dew points and gas inlet temperatures. However, the physical facts are so vast we decided to omit the illustration. Please contact our experts for clarification or refer to our calculation programme.

Heat exchanger overview

Heat exchanger	2x MTG-2 ³⁾ 2x MTG-2-I ^{2) 3)}	2x MTV-2 ³⁾ 2x MTV-2-I ^{2) 3)}
Materials in contact with media	Glass PTFE	PVDF
Flow rate v_{\max} ¹⁾	210 NI/h	190 NI/h
Inlet dew point $\tau_{e,\max}$ ¹⁾	70°C	70°C
Gas inlet temperature $\vartheta_{G,\max}$ ¹⁾	140°C	140°C
Max. Cooling capacity Q_{\max}	80 kJ/h	65 kJ/h
Gas pressure p_{\max}	3 bar	2 bar
Pressure drop Δp ($v=150 \text{ L/h}$)	19 mbar	18 mbar
Dead volume V_{tot}	38 ml	36 ml
Gas connections (metric)	GL14 (6 mm) ⁴⁾	DN 4/6
Gas connections (US)	GL14 (1/4") ⁴⁾	1/4"-1/6"
Condensate out connection (metric)	GL18 (8 mm) ⁴⁾	G1/4
Condensate out connection (US)	GL18 (8 mm) ⁴⁾	NPT 1/4"

¹⁾ Max. cooling capacity of the cooler must be considered.



²⁾ Models marked I have NPT threads or US tubes, respectively.

³⁾ Passive discharge via automatic condensate drains or traps not applicable for MTG-2 heat exchangers. For passive discharge on MTV-2 heat exchangers, use a screw connection with a clearance of at least 7 mm (see accessories).

⁴⁾ Gasket inside diameter.

Dimensions (mm)

Models for standard applications (TC-Standard+ 612x):



S1 = Electric supply
S2 = Status output
S3 = Analog output

Ordering instructions

Gas cooler model with two heat exchangers in series

The item number is a code for the configuration of your unit. Please use the following model code:

4496	2	1	2	X	2	X	1	X	X	X	0	X	X	X	0	0	0	0	Product Characteristics
Gas cooler models (with 2 in-line heat exchangers)																			
1				TC-Standard+ 6121 X2 Ambient temperature 40 °C															
2				TC-Standard+ 6122 X2 Ambient temperature 50 °C															
Certifications																			
2				for explosive areas															
Supply voltage																			
1				115 V AC, 50/60 Hz															
2				230 V AC, 50/60 Hz															
4				24 V DC															
Heat exchanger																			
1 2 2				Duran glass, 2x MTG-2, metric															
1 2 7				Duran glass, 2x MTG-2-I, US															
1 3 2				PVDF, 2x MTV-2, metric															
1 3 7				PVDF, 2x MTV-2-I, US															
Condensate drain ¹⁾																			
0 0				without condensate drain															
2 0				CPdouble X2 with hose nipple, angled															
4 0				CPdouble X2 with screw connection ³⁾															
Moisture detector/filter																			
0 0				without filter, without moisture detector															
0 1				without filter, 1 moisture detector with PVDF adapter ²⁾															
1 0				1 filter, without moisture detector															
1 1				1 filter with built-in moisture detector															
Signal outputs																			
0 0				status output only															
1 0				Analog output, 4...20 mA additional															

¹⁾ 24 V DC CPdouble not connected electrically.

²⁾ Also available in stainless steel.

³⁾ Metric or US connection, per heat exchanger.

Consumables and accessories

Item no.	Description
4510008	Automatic condensate drain AK 5.2 (pressure operation only)
4510028	Automatic condensate drain AK 5.5 (pressure operation only)
4410004	Automatic condensate drain AK 20 (pressure operation only)
4410001	Automatic condensate drain 11 LD V 38 (pressure operation only)
41030050	Replacement filter element F2; 5-pack
9144050038	Cable for cooler temperature analog output 4 m
4410005	Condensate trap GL1, 0.4 L
44920035012	Condensate pump replacement hose, Tygon (Norpren), angled hose nipple
44920035016	Condensate pump replacement hose, Tygon (Norpren), angled hose nipple and screw connection (metric)
44920035017	Condensate pump replacement hose, Tygon (Norpren), angled hose nipple and screw connection (US)
4381045	Screw connection G1/4 – DN 8/12 for passive condensate connection MTS or MTV(-2)
4381048	Screw connection NPT 1/4" for passive condensate connection MTS-I or MTV(-2)-I